



DIAMONDS CARBIDES POLISHERS & MORE

2020

Content

- 4 **NEODIAMOND.** - Sterile Diamonds
- 8 **NEOBURR.** - Sterile Carbides
- 14 **NEOSHINE.** - Sterile Polishers
- 18 **NEODRYS.** - Parotid Saliva Control
- 20 **PROXI-CHEK.** - Interproximal Marker
- 22 **BITE-CHEK.** - Handled Articulation Film
- 24 **FLAPS.** - Cushioned Bite Tabs

Awards



About Us

From father & son to the leader in SPU Burs!

Our story begins with Thom Maass Sr. and Thom Maass Jr. in 1970 looking for a way to get into the dental industry. Their initial product line started with miniature x-ray materials, hence the name Microcopy. After spending years in dentistry (set in the backdrop of the HIV/AIDs epidemic) they noticed a glaring opportunity in the way burs were reused and sterilized multiple times.

The Maass' sought to revolutionize the dental industry with burs that performed as well as the leading brands while preventing the risk of cross contamination. They were adamant to offer burs at a more economic price that didn't require the time consuming steps of cleaning and sterilizing. The NEODIAMOND pre-sterilized Single-Patient-Use bur was born! To this day it is still the leading SPU diamond in the dental industry.

Our mission

We are committed to making a positive difference in the lives of dental practitioners and patients worldwide by bringing products to the market that make dentistry easier and safer. We strive to provide products that enable dentists to fulfill a social responsibility to provide better, healthier patient care. We seek to provide a greater sense of satisfaction to each of our global customers by offering truly innovative, effective and high-value products and solutions supported by excellent quality and customer service.


Paul Tucker
CEO



INSTA NEG/FIX 1970



NEODIAMOND 1989

Take us for a **FREE** test drive!
Scan or visit MicrocopyDental.com/Samples
for up to date offers and product information.



NEODIAMOND®

"Cuts like a hot knife through butter" – NEODIAMOND User

20% more diamond exposure combined with advanced Triton® bonding technology means superior hardness and longevity all while helping you achieve the precise, crisp margins you expect from a single-patient-use diamond.

They make Rolexes and burs?

You heard correctly, the same country that makes the finest timepieces in the world also makes the XactFit® shank that is unique to NEODIAMOND. Swiss-made XactFit shanks ensure integrity and adhere to the strictest shank diameter tolerances in the industry. No walking out of the hand-piece issues here.



Clean as a whistle...Actually cleaner than any whistle

Each NEODIAMOND is gamma-sterilized and individually wrapped and packaged in a clear poly packet. Pop the pouch, fit into hand-piece and do your thing knowing you won't be cross contaminating the area.

"I've tried other brands...
But always return to NEODIAMOND."

Edward Berger DMD,
Atlanta, GA

NEW Z-CLASS ZIRCONIA BURS

Introducing Z-Class

Uniquely designed burs with zirconia cutting and adjusting in mind.

Make zirconia frustration a thing of the past!



Coarse		Fine		PURPLE HEADER		MAGENTA HEADER		TEAL HEADER		DARK BLUE HEADER	
C	150µ	F	50µ								
Coarse	C 130µ	Very Fine	Vf 30µ								
Medium	M 100-110µ	Z-Class	Z	\$98.85	\$3.95	\$65.95	\$6.60	\$44.85	\$4.49	\$69.95	\$2.80
				25 per pack	per piece	10 per pack	per piece	10 per pack	per piece	25 per pack	per piece

NEODIAMOND®

SPECIALTY DIAMONDS

NEOSPIRAL

25 per pack

Round End Taper

Football

8114.8 C	8116.8 C	8116.10 C	8118.7 C	8118.9 C	8923 C
856-014	856-016	856-016	856-018	856L-018	368-023
1.4 / 8.0 / 0.9	1.6 / 8.0 / 1.1	1.6 / 10.0 / 1.1	1.8 / 7.0 / 1.4	1.8 / 9.0 / 1.4	2.3 / 5.2
19.7	19.7	21.7	18.7	20.7	19.9

GUIDE PIN

10 per pack

Round End Taper

ENDO ACCESS

10 per pack

Round End Taper

GP9.016 C F	GP9.021 C F	GP9.023 C F	E164.011 C	E164.015 C	E165.014L C
508C-016	508C-021	508C-023	164-011	164-015	165-014L
1.6 / 9.0 / 1.3	2.1 / 9.0 / 1.7	2.3 / 9.0 / 1.9	1.9 / 10.0 / 1.1	1.9 / 10.0 / 1.5	1.4 / 8.0 / 1.0
21.0	21.0	21.0	21.0	21.0	21.0

END CUTTER

10 per pack

DEPTH CUTTER

FINISHING

25 per pack

End Cutter

Depth Cutter

Round End Taper

Pointed Cone

Flame

Egg

Football

5012 M	5014 M	5016 M	6005 M	7003 M	7005 M	3116.8 VF	3310.3 VF	3314.8 VF	3314.10 VF	3512.7 VF	3512.8 VF	3512.10 VF	3516.8 VF	3900 VF	3916 VF	3923 VF
10839-012	10839-014	10839-016	828-026	834-016	834-021	856-016	858-008	858-014	859-014	861-012	862-012	863-012	862-016	379-023	368-016	368-023
1.2	1.4	1.6	0.5 depth	0.3 depth	0.5 depth	1.6 / 8.0 / 1.0	0.8 / 3.0	1.4 / 8.0	1.4 / 10.0	1.1 / 7.0	1.2 / 8.0	1.2 / 10.0	1.6 / 8.0	2.3 / 4.2	1.6 / 3.2	2.3 / 5.2
21.1	21.1	21.1	19.2	22.1	22.1	19.6	22.0	19.4	21.4	21.0	19.5	21.5	19.5	19.0	19.0	19.8

NEW

Z-CLASS ZIRCONIA BURS

Introducing Z-Class

Uniquely designed burs with zirconia cutting and adjusting in mind.

Make zirconia frustration a thing of the past!

ADJUSTERS

25 per pack

Ball

Round End Taper

Teardrop

Pointed Cone

Needle

Flame

Egg

0123ZA Z	1116ZA Z	1231ZA Z	1310ZA Z	1510ZA Z	1514ZA Z	1900ZA Z
2.2 / 2.0	1.6 / 9.0	2.9 / 6.2	0.9 / 11.0	0.9 / 4.0	1.4 / 2.7	2.1 / 5.2
19.0	22.0	20.0	24.0	23.0	19.0	19.0

CUTTERS

25 per pack

Round End Cylinder

Round End Taper

1212Z Z	1214Z Z	1116Z Z
1.2 / 8.0	1.4 / 8.0	1.6 / 8.0
22.0	22.0	22.0

#1 Single-Patient-Use Diamond

Highest rated, best performing, single-patient-use diamond.



Pricing

PINK HEADER

\$48.50

25 per pack

\$1.94

(per piece)

DARK BLUE HEADER

\$69.95

25 per pack


\$2.80

(per piece)


Packs

25 per pack

Shank



Short Shank (S)
16.1 mm to 17.6 mm



Standard Shank
18.1 mm to 22.5 mm

Grits

Coarse **G** 150µ

Coarse **G** 130µ

Medium **M** 100-110µ

Fine **F** 50µ

Reference FG

Head Dia/ Lgth / Tip (mm)

OAL (mm)

Ball

(1/2)	(1)	(2)	(4)	(6)	(8)
0106 (S)	0110	0112	0116	0118	0123
FS	M	M	CM	CM	CF
S801-006	801-010	801-012	801-016	801-018	801-023
0.6 / 0.6	1.0 / 0.8	1.2 / 1.0	1.6 / 1.4	1.8 / 1.6	2.3 / 2.0
16.5	19.1	19.2	19.2	19.2	17.4

Inverted Cone

0312	0316	0316.4	0318.5	0416
M	C	C	C	C
805-012	805-016	807-016	807-018	813-014
1.2 / 0.9	1.6 / 1.4	1.6 / 4.0	1.8 / 5.0	1.4 / 2.2
19.2	19.2	19.2	19.2	19.2

Pear

0508 (S)	0508	0512 (S)	0512
MS	M	MS	CM
S830-008	830-008	S830-012	830-012
0.8 / 1.6	0.8 / 1.6	1.2 / 3.0	1.2 / 3.0
16.1	19.1	16.2	19.0

Flat End Cylinder

0708.3 (S)	0710 (S)	0710	0712	0712.7	0716.8	0614.8
FS	CS MS	CM	C	C	C	CF
S835-008	S835-010	835-010	835-012	837-012	837-016	837KR-014
0.8 / 3.0	1.0 / 4.0 / 1.0	1.0 / 4.0 / 1.0	1.2 / 4.0 / 1.2	1.2 / 7.0 / 1.2	1.6 / 8.0 / 1.6	1.4 / 8.0 / 1.4
16.5	16.2	19.2	19.2	19.2	19.7	20.2

Round End Cylinder

1207.2 (S)	1210.7	1212.7	1214.8
FS	CF	C	C
S881-007	881-009	881-012	881-014
0.7 / 2.0	0.9 / 7.0 / 0.9	1.2 / 7.0 / 1.2	1.4 / 8.0 / 1.4
16.5	19.1	18.7	19.7

Beveled Cylinder

1800.8	1804.8	1812.8	1812.10
CF	C	CM F	CM
878-012	878-014	885-012	886-012
1.2 / 8.0 / 1.2	1.4 / 8.0 / 1.4	1.2 / 8.0 / 1.2	1.2 / 10.0 / 1.2
19.6	20.1	19.6	21.6

Modified Flat End Taper

0816.6 (S)	0816.8	0818.4	0818.8	2525
CS MS	CM F	CM	C	M
S846KR-016	847KR-016	845KR-018	847KR-018	845KR-025
1.6 / 6.0 / 1.1	1.6 / 8.0 / 1.1	1.8 / 4.0 / 1.4	1.8 / 8.0 / 1.4	2.5 / 4.0 / 2.0
16.7	20.3	18.1	20.3	18.0

Flat End Taper

0914.8	0914.9	0916.8	0916.10	0918.8	0918.10
CM F	C	CM F	CM	CM	CM
847-014	847L-014	847-016	848-016	847-018	848-018
1.4 / 8.0 / 1.0	1.4 / 9.0 / 0.7	1.4 / 8.0 / 1.2	1.6 / 10.0 / 1.1	1.8 / 8.0 / 1.4	1.8 / 10.0 / 1.4
19.7	20.6	19.7	21.7	19.8	21.7

Round End Taper

1112.7	1112.10	1113.7 (S)	1114.6 (S)	1114.8	1114.10	1116.6 (S)	1116.7	1116.8	1116.10	1118.7	1118.8	1118.9	1121.8	1122.8
CM	CM	MS FS	CS	CM F	CM F	CS MS	CM	CM F	CM F	CF	C	CM F	C	C
S850-012	S850-012	S855-013	S855-014	856-014	850-014	S855-016	856-016	856-018	850-016	856-018	856-018	856L-018	856-021	856-022
1.2 / 7.0 / 0.7	1.3 / 10.0 / 0.7	1.3 / 6.6	1.4 / 6.0 / 0.9	1.4 / 8.0 / 0.9	1.4 / 10.0 / 0.9	1.6 / 6.0 / 1.1	1.6 / 7.0 / 1.1	1.6 / 8.0 / 1.1	1.6 / 10.0 / 1.1	1.8 / 7.0 / 1.4	1.8 / 8.0 / 1.2	1.8 / 9.0 / 1.4	2.1 / 8.0 / 1.6	2.2 / 8.5 / 1.8
18.6	21.7	16.5	16.7	19.7	21.6	16.7	18.5	19.7	21.7	18.7	22.0	20.7	19.9	22.5

Pointed Taper

1712.8	1712.10	1714.8	1714.10	1716.6 (S)	1716.8	1718.8	1718.10	1721.8
CM	CM	CM F	CM	CS MS	CM F	CF	C	C
878K-012	879K-012	878K-014	879K-014	S877K-016	878K-016	878K-018	879K-018	878K-021
1.2 / 8.0 / 0.8	1.2 / 10.0 / 0.8	1.4 / 8.0 / 1.0	1.4 / 10.0 / 1.1	1.6 / 6.0 / 1.2	1.6 / 8.0 / 1.2	1.8 / 8.0 / 1.4	1.8 / 10.0 / 1.4	2.1 / 8.0 / 1.6
20.1	22.1	20.1	21.6	17.1	20.1	20.1	21.6	20.1

Pointed Cone

1300 (S)	1310.3	1312.11	1314.8	1314.10	1416
FS	M F	CF	CM F	CM F	M F
S858-008	858-008	859-012	858-014	859-014	392-016
0.8 / 3.0	0.8 / 3.0	1.2 / 11.0	1.4 / 8.0	1.4 / 10.0	1.6 / 5.0 / 0.4
16.9	22.0	24.0	19.5	21.5	19.0

Interproximal

Flame

1507.2 (S)	1509.3	1510.8	1512.6 (S)	1512.7
FS	M F	CM F	CS MS	C
S862-007	889-009	862-010	S862-012	861-102
0.7 / 2.2	0.9 / 3.0	1.0 / 8.0	1.2 / 6.0	1.2 / 7.0
16.5	20.0	20.0	17.6	21.0

Egg

1512.8	1512.10	1514.7	1514.8	1516.8	1518.9
CM F	CM F	CM	C	CM F	CF
862-012	863-012	862-014	862-014	862-016	862L-018
1.2 / 8.0	1.2 / 10.0	1.4 / 7.5	1.4 / 8.0	1.6 / 8.0	1.8 / 9.0
19.6	21.6	19.0	19.6	19.5	20.4

Football

1908	1900	1916	1920	1923
CF	CM F	CF	CF	CM F
379-018	379-023	368-016	368-020	368-023
1.8 / 3.4	2.3 / 4.2	1.6 / 3.2	2.0 / 5.0	2.3 / 5.2
18.7	19.2	19.2	20.0	19.9

Wheel

2035	2042
C	C
909-035	909-042
3.5 / 1.3	4.2 / 1.5
16.7	17.5

Occlusal Reduction

2133	2137
C	C
811-033	811-037
3.3 / 5.0	3.7 / 7.0
19.7	21.7

Gross Reduction

2217	2218
C	C
6051-017	6055-018
1.7 / 8.0 / 1.7	1.8 / 8.0 / 1.3
20.3	20.2



NEOBURR®

The greatest invention since sliced bread

More blade contact with the tooth means fantastic cutting ability without clogging up the blades.

We don't have a breaking point

Blended Neck® technology on most NEOBURR carbides provide superior strength and durability. Being constructed with a single piece of material eliminates the weld that is often the point which other burs separate. No breaking point here.

Testing, testing 1-2-3

We tested it but others did too. In 3rd party testing our 557² carbide was shown to be up to 70% stronger than the competition.

Nobody likes a chatter box.

With its unique construction NEOBURR provides a fast, smooth, chatter-free experience. This is good for you and your hand-piece.

"Love your product.
Price and packaging, quality of
cut, all exceeds my expectations."

E. Rothfield DDS,
Hollywood, FL

VARIETY IS THE SPICE OF LIFE

We offer carbides in various
styles to handle all your
procedural needs!



RIGHT TOOL FOR EVERY JOB

NEOBURRS are grouped into eight categories for different applications. Six shank types are available, FG, SS, FGSL, RA, RASL, and HP. Head diameter is measured at the head's widest part.

OPERATIVE 16.5 - 22.0 mm

An extensive range of popular sizes of 6-blade burs are available in FG and RA (right angle-latch type shanks).



FG8

SURGICAL LENGTH 25.0 - 26.0 mm

The most popular sizes of surgical length 6-blade burs in FG and RA shanks.



FGSL557

NEOMAX METAL CUTTERS 19.0 mm

Two sizes of metal/crown cutter specialty burs in FG shanks. Gold-plated finish.



MAX 2

TRIMMING & FINISHING 19.0 - 24.0 mm

The most popular sizes of 12-blade FG burs designed for trimming, shaping and finishing all restorative materials. Gold-plated finish.



7901

CROWNKING CROWN PREP 19.0 - 20.3 mm

6-blade crown preparation specialty burs in FG shanks. Gold-plated finish.



CK85616

30-BLADE FINISHING 19.0 mm

Gold-plated carbides utilize precision engineered blades to achieve vibration-free, ultra-smooth finishing.



9103UF

SURGICAL 23.0 - 28.0 mm

These 4 and 6-blade carbides are designed to cut bone, or prepare Endo Access to the pulp chamber. FG shank.



152

ORAL SURGERY HP 44.5 mm

A range of 6-blade popular shapes. Fits HP hand-piece (shank #1).



HP 1702

CARBIDE PRICING

PINK HEADER				PURPLE HEADER				DARK BLUE HEADER				BLUE HEADER			
50 FG SS 50 per pack	\$98.85	1.93 per piece		50 RA 50 per pack	\$100.35	\$2.00 per piece		25 FG 25 per pack	\$79.50	\$3.18 per piece		10 HP 10 per pack	\$42.75	\$4.28 (per piece)	
10 FG SS 10 per pack	\$20.55	\$2.06 per piece		10 RA 10 per pack	\$21.35	\$2.14 per piece		10 FG 10 per pack	\$34.00	\$3.40 per piece		10 FG 10 per pack	\$87.50	\$8.75 per piece	
YELLOW HEADER				RED HEADER				TEAL HEADER							
25 FG 25 per pack	\$80.60	\$3.22 (per piece)		25 RA 25 per pack	\$83.75	\$3.35 (per piece)		25 FG 25 per pack	\$152.95	\$6.12 (per piece)					
10 FG 10 per pack	\$34.45	\$3.45 (per piece)		10 RA 10 per pack	\$35.60	\$3.58 (per piece)		10 FG 10 per pack	\$67.05	\$6.71 (per piece)		5 FG 5 per pack	\$75.00	\$15.00 (per piece)	

Individually wrapped and highly
visible through a poly packet, each carbide is
identified by bur number and shape description.

New Definition of Strength®

Highest rated, best performing,
single-patient-use carbides.




Shanks

Shank Icon

Shank

OAL (Over All Length)


SS



Short Shank

16.1 mm to 16.5 mm


FG



Friction Grip Shank

19.0 mm to 28.0 mm


RA



Right Angle Shank

19.0 mm to 26.0 mm


FG



Friction Grip Surgical Length Shank

23.0 to 28.0 mm


RA



Right Angle Surgical Length Shank

25.0 mm

HP



HP (One / Straight Hand-piece) Shank

44.5 mm






















OPERATIVE

OAL 19.0mm

50

*10

*10pk only available
on selected shapes

Round		Inverted Cone							Straight Fissure				Tapered Fissure				Amalgam Prep				
																					
Shank:	1/4	1/2	1	2	4	6	8	33 ^{1/2}	34	35	36	37	56	57	58	169	169L	170	170L	245	
Reference #	1/4	1/2	1	2	4	6	8	33 1/2	34	35	36	37	56	57	58	169	169L	170	170L	245	
Head Dia/ Lgth (mm)	0.5 / 0.4	0.6 / 0.5	0.8 / 0.7	1.0 / 0.8	1.4 / 1.1	1.8 / 1.6	2.3 / 1.9	0.6 / 0.5	0.8 / 0.6	1.0 / 0.8	1.2 / 1.0	1.4 / 1.1	0.8 / 3.2	1.0 / 3.8	1.2 / 3.8	0.9 / 3.4	0.9 / 4.9	1.0 / 3.8	1.0 / 4.9	0.8 / 2.8	

Pear

Straight Fissure Crosscut

Tapered Fissure Crosscut

Round End Tapered Fissure

Round End Fissure

Round End Fissure Crosscut














329 FG	330 FG SS	331 FG SS	331L FG	332 FG	556 FG SS	557 FG SS	557L FG	558 FG	699 FG	700 FG	701 FG	701L FG	702 FG	1171 FG	1156 FG	1157 FG SS	1158 FG	1556 FG	1557 FG SS	1558 FG
329	330	331	331L	332	556	557	557L	558	699	700	701	701L	702	1171	1156	1157	1158	1556	1557	1558
0.6 / 0.9	0.8 / 1.9	1.0 / 1.8	1.0 / 3.7	1.2 / 2.0	0.8 / 3.2	1.0 / 3.8	1.0 / 4.9	1.2 / 3.8	0.9 / 3.4	1.0 / 3.8	1.2 / 3.8	1.2 / 4.9	1.6 / 4.3	1.2 / 3.8	0.8 / 3.2	1.0 / 3.8	1.2 / 3.8	0.8 / 3.2	1.0 / 3.8	1.2 / 3.8

SURGICAL LENGTH

OAL 23.0 to 28.0mm

25

10

	Round							Straight Fissure Crosscut			Tapered Fissure Crosscut		
0 mm													
Shank:	SL 1/2 FG	SL1 FG	SL2 FG RA	SL4 FG RA	SL6 FG RA	SL8 FG RA		SL557 FG	SL558 FG		SL701 FG	SL702 FG	
Reference #	SL 1/2	SL1	SL2	SL4	SL6	SL8		SL557	SL558		SL701	SL702	
Head Dia/ Lgth (mm)	0.6 / 0.5	0.8 / 0.7	1.0 / 0.8	1.4 / 1.1	1.8 / 1.6	2.3 / 1.9		1.0 / 3.8	1.2 / 3.8		1.2 / 3.8	1.6 / 4.3	

METAL CUTTERS

OAL 19.0 mm

25

10

NEOMAX® Metal Cutters

Shank: MAX 1 FG	MAX 2 FG
Reference # GWI/1931	GW2/1958
Head Dia/ Lgth (mm) 1.0 / 1.9	1.2 / 4.0

CROWN KING

OAL 19.0 to 20.3 mm

25

10

Shank: CK85616 FG	CK85618 FG	CK84716 FG	CK37923 FG
Reference # 856-016	856-018	847-016	379-023
Head Dia/ Lgth. / Tip (mm) 1.6 / 8.0 / 1.2	1.8 / 8.0 / 1.5	1.6 / 8.0 / 1.2	2.3 / 4.3
OAL (mm) 20.3	20.3	20.3	19.0

New Definition of Strength®

Highest rated, best performing,
single-patient-use carbides.



ESTHETIC
FINISHERS

OAL 19.0 to 23.0mm

25

10









12-BLADE
TRIMMING
& FINISHING

OAL 19.0 to 23.0mm

25

10










Long Taper	Bullet				Needle		
------------	--------	--	--	--	--------	--	--

							
7642 FG	7664 FG	7675 FG	7802 FG	7803 FG	7901 FG	7902 FG	7903 FG
Reference #	7642	7664	7675	7802	7803	7901	7902
Head Dia/ Lgth (mm)	1.0 / 7.0	1.5 / 8.2	1.6 / 8.0	1.0 / 3.4	1.2 / 3.4	0.9 / 3.6	1.2 / 3.6
OAL (mm)	21.0	23.0	22.0	20.5	20.5	20.5	20.5

EF-Series 10 Straight-Blades	Egg 12 Spiral-Blades	Bullet 12 Straight-Blades
---------------------------------	-------------------------	------------------------------

						
EF3 FG	EF4 FG	EF6 FG	EF9 FG	OS1 FG	OS2 FG	OS3 FG
Reference #	EF3	EF4	EF6	EF9	(7801)	OS3
Head Dia/ Lgth (mm)	0.8 / 3.0	1.0 / 4.2	1.4 / 6.0	1.4 / 9.0	2.3 / 4.3	0.7 / 3.2
OAL (mm)	23.0	20.5	21.0	24.0	20.5	20.5

Round	Flame	Egg
-------	-------	-----

								
7006 FG	7104 FG	7106 FG	H274 FG	H48L10 FG	H48L12 FG	7404 FG	7406 FG	7408 FG
Reference #	7006	7104	7106	H274	H48L10	7404	7406	7408
Head Dia/ Lgth (mm)	1.8 / 1.6	1.4 / 3.4	1.8 / 3.7	1.6 / 3.5	1.0 / 8.0	1.2 / 8.0	1.4 / 3.3	2.3 / 3.9
OAL (mm)	19.0	19.0	19.0	19.0	22.0	22.0	19.0	19.0

30-BLADE
TRIMMING
& FINISHING

OAL 19.0 to 23.0mm

5

SURGICAL

OAL 23.0 to 28.0mm








5

HP ORAL
SURGERY






OAL 44.5 mm

10







Tapered Fissure Crosscut	Round Fissure Crosscut	Round Tapered Fissure Crosscut
-----------------------------	---------------------------	-----------------------------------

						
HP 701 HP	HP 702 HP	HP 703 HP	HP 1557 HP	HP 1702 HP	HP 1703 HP	HP 1703L HP
Reference #	HP 701	HP 702	HP 703	HP 1557	HP 1702	HP 1703
Head Dia/ Lgth (mm)	1.2 / 3.8	1.6 / 4.3	2.1 / 4.8	1.0 / 3.8	1.6 / 4.4	2.1 / 4.9
OAL (mm)	44.5	44.5	44.5	44.5	44.5	44.5

Esthetic Finisher	Interproximal	Pointed Taper	Egg	Needle
----------------------	---------------	------------------	-----	--------

					
Shank:	EF9UF FG	9103UF FG	9214UF FG	9406UF FG	9903UF FG
Reference #	EF9UF	9103UF	9214UF	9406UF	9903UF
Head Dia/ Lgth (mm)	1.4 / 9.0	1.2 / 3.6	1.0 / 5.6	1.8 / 3.4	1.2 / 3.6
OAL (mm)	24.0	19.0	22.0	19.0	21.0






151Z	Lindemann Straight	Crosscut	ENDO ACCESS	Endo Access
------	-----------------------	----------	----------------	----------------

						
Shank:	151Z FG	151LZ FG	161 FG	162 FG		152 FG
Reference #	151Z	151LZ	161	162		152
Head Dia/ Lgth (mm)	1.6 / 11.0	1.6 / 11.0	1.6 / 10.0	1.6 / 10.0		1.6 / 9.0
OAL (mm)	23.0	28.0	25.0	25.0		23.0

OAL 23.0 mm

Safe-End

Round	Straight Fissure Crosscut
-------	------------------------------

					
Shank:	HP 2	HP 4	HP 6	HP 8	HP 557
	HP	HP	HP	HP	HP
Reference #	HP 2	HP 4	HP 6	HP 8	HP 557
Head Dia/ Lgth (mm)	1.0 / 0.8	1.4 / 1.1	1.8 / 1.6	2.3 / 1.9	1.0 / 3.8
OAL (mm)	44.5	44.5	44.5	44.5	44.5

NEOSHINE®

Frustrated with polishing?

Look, every dentist can agree that when it comes to polishers, things can get more confusing than advanced college calculus. We know how you feel, dentists want a polishing system that's simple and that works.

Name a surface, we've got a polisher for that!

Introducing the cool new kid in class, NEOSHINE from MICROCOPY. Comprised of three polishers for use on Composite, Metal, and Zirconia. NEOSHINE's easy Color ID system organizes polishers by materials and steps. Most importantly, NEOSHINE achieves a smooth mirror-like shine like nobody's business.

Easy like Sunday morning

NEOSHINE sterile polishers are a simple two-step system to make for a sweet shiny polish. It's cups and points, are mini size – meaning you can literally polish anywhere. Plus, flexible discs provide the right finishing touch to soft and hard materials. Take it for a test drive!

- Polishes to a smooth mirror-like finish.
- Easy Color ID system helps you pick the right polisher for the right surface.
- Miniature size enables you to thoroughly polish all tooth anatomy.

"The speed of polishing and quality of the resulting surface finish are second to none!"

Joshua Howard DMD
Dover, NH

SURFACE TO SURFACE

Name the surface. We have a polisher to handle it.



HOLD ME CLOSER TINY POLISHER (MINI POLISHERS THAT GET HUGE RESULTS)

Comprised of three polishers for use on Composite, Metal, and Zirconia, NEOSHINE's easy Color ID system organizes polishers by materials and steps. But most importantly, NEOSHINE achieves a smooth mirror-like shine like nobody's business.

COMPOSITE		METAL		ZIRCONIA	
					
Step 1 NS-C CUP 1 NS-C POINT 1	Step 2 NS-C CUP 2 NS-C POINT 2	Step 1 NS-M CUP 1 NS-M POINT 1	Step 2 NS-M CUP 2 NS-M POINT 2	Step 1 NS-Z CUP 1 NS-Z POINT 1	Step 2 NS-Z CUP 2 NS-Z POINT 2
\$24.95 20 per pack	\$45.95 20 per pack	\$24.95 20 per pack		\$47.95 20 per pack	


Instructions for Use

Step 1: apply light pressure.

Step 2: apply feather light pressure.

- All Polishers (Recommended Speed) 7,000 rpm.
- Max speed 20,000 rpm.*
- Polishing paste is not required.
- Spray water at least every 10 to 15 seconds to avoid excess heat build-up.
- For single-patient-use.

*Avoid long periods of applied pressure as heat generation can cause damage to the margins. Insufficient water cooling can lead to irreversabile damage to the tooth pulp or its surrounding tissue.



Step 1
Light Pressure



Step 2
Feather Light Pressure

Single use

mcifu.com

NEOSHINE®

Composite / Porcelain
Disc

Fine

Medium

Coarse

Very
Coarse

Check out our Polishing playlist

CD's? Records? What do they have in common? They are spinning discs that play music. While these discs are now "old school", disc polishers are not! Introducing a new kind of disc to rock your world, NeoShine Disc Polishers.

Make it snappy!

Being snap-on single-use discs with a reusable mandrel, these disc polishers are designed to make your life simple (and who doesn't like simplicity these days?). Available in two sizes, 10 and 14mm, NeoShine Discs can polish composite, metal, and porcelain, allowing you to easily reach those nooks and crannies on a variety of materials.

Let's make beautiful music together

This polishing system comes in a package of 100 discs with one mandrel. Mandrel refills are also available for purchase. So, what are you waiting for? Time to make some sweet polishing music!

Composite/Porcelain
Coarse & Very Coarse




MAN(DREL) OF STEEL

All kits come with a high quality super strong stainless steel mandrel.



FRESH SPIN ON POLISHING (FLEXIBLE DISC ADJUST TO ANY PROCEDURE)

COMPOSITE / PORCELAIN - DISC




(10mm) (14mm)
NS-CP DISC10 NS-CP DISC14

\$39.95

One size per pack of 100 pcs.
(25 pcs. per grit) + 1 mandrel

COMPOSITE / METAL - DISC



(10mm) (14mm)
NS-CM DISC10 NS-CM DISC14

\$49.95

One size per pack of 100 pcs.
(25 pcs. per grit) + 1 mandrel

MANDREL REFILL



NS-MANDREL-D

\$10.95
3 per pack

Instructions for Use

- **Composite/Porcelain:** Very Coarse, Coarse, Medium, & Fine.
- **Composite/Metal:** Very Coarse, Coarse, Medium, & Fine.
- **Recommended Speed:** 10,000 rpm **Max speed:** 20,000 rpm.*
- Polishing paste is not required.
- Keep the disc dry and cool tooth with air at least every 10 to 15 seconds to avoid excess heat build-up.

**Avoid long periods of applied pressure as heat generation can cause damage to the tooth.
Improper use of these instruments may lead to poor results and increased patient risk.*



Composite/Metal
Very Coarse
& Coarse
shown

Single use

mcifu.com

"The speed of polishing
and quality of the resulting surface
finish are second to none!"

Joshua Howard DMD
Dover, NH

Suck it up buttercup

NEODRYS saliva absorbents do just that! We know how important it is to work in a dry field when doing the procedures you do all day long. Built with a super absorbent core ensures things stay nice and dry.

To serve and protect (the cheek that is)

NEODRYS protective backing and our patented design gives you great cheek retraction. You have room to do what you need to do in close quarters, plus they protect the cheek in case you have a runaway bur situation.

Reflect on your bad choices...

And make some improvements! With a reflective backing option, NEODRYS reflective brightens up the oral cavity and ensures you see exactly what you're working with. Out of the darkness and into the light!



ANATOMY OF ABSORPTION

(HERES WHY WE'RE BETTER)

CORE STIFFENER

Stiffener insert provides optimum rigidity for cheek retraction.

SUPER ABSORBENT CORE

Acrylate polymer traps moisture as a gel when in contact with saliva.

GENTLE TO THE BUCCAL MUCOSA


Medical-grade poly netting adheres gently to tissue.

"OUCHLESS" COMFORT EDGE®

New technology creates a soft, flexible edge with no sharp corners while retaining product integrity.

PROTECTIVE BACKING

Choice of Original white or Reflective backing brightens the oral cavity while providing cheek protection.



PRICING



WHITE BACKING


\$13.95 | Small Original
50 per pack | Large Original




REFLECTIVE BACKING

\$14.95 | Small Reflective
50 per pack | Large Reflective


Instructions for Use



Color to Cheek



Point to Back



Spray to Release



Single use



mcifu.com



15 min
Absorption

TIME IS MONEY

15 minutes of absorption
saves you on both.



"A must have product for day in - day out dentistry today."

Andrew Bargren DDS,
Hollywood, FL

PROXI-CHEK®

Adjustment on a stick?

Yep, we did that. Knowing precisely where to adjust a crown interproximally is critical to the success of your procedure. Nobody likes playing the "Guess and Check" game!

Precise marks produce perfect fitting crowns

PROXI-CHEK uses a thin film that leaves a black mark through friction on the point of contact. With such a visible mark, it is easy to quickly reduce "too tight" areas and create broad contacts. In addition, PROXI-CHEK can mark on all types of prostheses and teeth. PROXI-CHEK makes placement procedures easier.

- Single-use, economical interproximal marker.
- Remove the guess and check work from seating a crown.
- Marks all types of crowns (zirconia, porcelain, lithium disilicate and metal).

Double-sided black film
19 microns thick

"Very simple and elegant product to locate tight contact areas. Not messy like sprays and more accurate than using floss."

Philip Rader DDS,
Hixson, TX

MAKE YOUR MARK

With Proxi-Chek you can guarantee a visible and precise mark.



GET A HANDLE ON MARKING (GET IT? GET A HANDLE!)

MARKING FILM


Thin black film precisely marks points of contact to eliminate the guesswork in adjustments.

HANDLE

Easy-grip handle is made to reach the posterior molars.

BENDABLE FOR POSTERIOR

Handle bends at 90° for posterior crowns.



Patent Pending

PRICING



Black Double-Sided Film
19 microns


PROXI-CHEK

\$28.00
45 per pack

Instructions for Use



Dry working area.



Face crease up, pinch down and release.



Position film and place prosthesis. Slightly tug to create mark.



Remove prosthesis. Adjust and repeat as needed.

Single use mcifu.com

BITE•CHEK[®]

You can handle this

We know your time is precious. Why waste it dealing with forceps? BITE-CHEK provides precise marking with its built in handle design. Film with a handle—no forceps needed!

Ready. Set. Bite!

BITE-CHEK accurately marks the points of contact, minimizing the possibility of high occlusion and post-operative sensitivity. Pull it out of the pack. Use it. Then discard! Yep, it's that simple!

- Thin film marks high points accurately – works best on a dry surface.
- Marks all surfaces: enamel, metal, non-metal restorations, and plastic.
- Available in double-sided film, Black/Black and Red/Black.

Double-sided film
19 microns thick

"This is a "why didn't I think of that?" product. It is a simple solution executed to perfection. Congrats!"

Dental Arts of Sunset,
Miami, FL

FORCEPS-FREE ZONE

We've eliminated the need for forceps with our built in handle. That's one less thing you have to deal with.



WE ALSO HANDLE ADJUSTMENTS (ANOTHER HANDLE PUN...SORRY)

CURVED

Made to fit the curve of the oral cavity.

CURL-FREE

No curling, handle holds film flat.

MARKING FILM

Thin black film precisely marks points of contact to eliminate the guesswork in adjustments.

The double-sided Red/Black film makes it possible to mark both occlusion and excursion.

HANDLE

Easy-grip handle is designed to reach the posterior molars.

ADJUSTABLE FULL ARCH

Hold two Bite-Chek side-by-side to mark the full arch. The angle can be adjusted to fit the width of the arch.



Patented
USD733302 S1


PRICING



BC-BLACK

\$17.95

100 per pack




BC-RED/BLACK


\$17.95

100 per pack


Instructions for Use



Dry the tooth surface.



Position film on teeth.



Check occlusion.

Single use mcifu.com

FLAPS®

Simple as that!

Self-sticking foam tabs attach quickly and are easy to position.

We're on point


Cushioned tab holds film or sensor securely, allows full occlusion and provides visual reference for accurate placement and alignment.

Tooth pillows?

Soft cushioning without hard surfaces, provides the ultimate in comfort and small size reduces gagging.

Kick 'em to curb

Use-and-toss convenience—extremely cost effective too!



PRICING



ORIGINAL (WHITE)

\$41.25

500 per pack



LONG (BLUE)

\$41.25

375 per pack

ORIGINAL (WHITE)





Perfect for horizontal or vertical bitewings.

LONG (BLUE)



Excellent for any periapical x-ray, using either the parallel or bisecting angle technique.

Instructions for Use



Single use

mcifu.com

Step 1: Stick the Flaps on the back of the film or sensor. (See diagram).

Step 2: Instruct patient to position tongue against sensor and bite onto Flaps.

Step 3: Ask for a raise because you've just upped your x-ray taking game.

Required: Snug-fitting sensor sheaths!

KIDS DIG US

Soft cushion keeps all patients comfortable (especially kids).



"Flaps are very easy, simple, and fast to use. Plus, patients don't gag like they do with other devices."

Tamara Simac RDA



TAKE US FOR A TEST DRIVE

(ONLY IF YOU'RE INTERESTED IN BETTER DENTAL PRODUCTS)

Call, Scan or Visit:

800.235.1863

MicrocopyDental.com



JOIN THE M-CROWD

Download our app to get exclusive promotions and stay up to date on the products you love!

Microcopy P.O. Box 2017 Kennesaw, GA 30156-9017